

For Scintillation Counting and High Energy Physics 51 mm (2 Inch) Diameter, Fast Time Response, Bialkali Photocathode, 10-stage, Head-on Type

GENERAL

Parameter		Description/Value	Unit
Spectral Response		300 to 650	nm
Wavelength of Maximum Response		420	nm
Photocathode	Material	Bialkali	—
	Minimum Effective Area	φ46	mm
Window Material		Borosilicate glass	—
Dynode	Structure	Linear focused	—
	Number of Stages	10	—
Base		14-pin base JEDEC No. B14-38	—
Operating Ambient Temperature		-30 to +50	°C
Storage Temperature		-30 to +50	°C
Suitable Socket		E678-14W (Sold Separately)	—

MAXIMUM RATINGS (Absolute Maximum Values)

Parameter		Value	Unit
Supply Voltage	Between Anode and Cathode	1600	V
	Between Anode and Last Dynode	350	V
Average Anode Current		0.1	mA

CHARACTERISTICS (at 25 °C)

Parameter		Min.	Typ.	Max.	Unit
Cathode Sensitivity	Luminous (2856 K)	60	90	—	μA/lm
	Blue Sensitivity Index (CS 5-58)	—	10.5	—	—
	Radiant at 420 nm	—	85	—	mA/W
	Quantum Efficiency at 420 nm	—	26	—	%
Anode Sensitivity	Luminous (2856 K)	20	90	—	A/W
	Radiant at 420 nm	—	8.5 × 10 ⁴	—	A/W
Gain		—	1.0 × 10 ⁶	—	—
Anode Dark Current (after 30 minutes storage in darkness)		—	5	20	nA
Time Response	Anode Pulse Rise Time	—	3.4	—	ns
	Transit Time Spread (FWHM)	—	3.6	—	ns
Pulse Linearity (at ± 2 % Deviation)*		—	150	—	mA

NOTE: Anode characteristics are measured with the voltage distribution ratio "A" except for Pulse Linearity.

* Measured with the special voltage distribution ratio "B".

VOLTAGE DISTRIBUTION RATIO "A"

Electrodes	K	Dy1	Dy2	Dy3	Dy4	Dy5	Dy6	Dy7	Dy8	Dy9	Dy10	P
Ratio	2	1	1	1	1	1	1	1	1	1	1	1

Supply Voltage: 1250 V, K: Cathode, Dy: Dynode, P: Anode

SPECIAL VOLTAGE DISTRIBUTION RATIO "B" FOR HIGH PULSE LINEARITY

Electrodes	K	Dy1	Dy2	Dy3	Dy4	Dy5	Dy6	Dy7	Dy8	Dy9	Dy10	P
Ratio	2	1	1	1	1	1	1.2	1.5	2.2	3.6	3	
Capacitors(μF)	—	—	—	—	—	—	0.01	0.01	0.01	0.01	0.02	

Supply Voltage: 1500 V, K: Cathode, Dy: Dynode, P: Anode

PHOTOMULTIPLIER TUBE R2154-02

Figure 1: Typical Spectral Response




Figure 2: Typical Gain Characteristics






Figure 3: Dimensional Outline and Basing Diagram (Unit: mm)



Socket E678-14W
(Sold Separately)



TPMHA0296EB

TACCA0200EA

HAMAMATSU

WEB SITE www.hamamatsu.com

HAMAMATSU PHOTONICS K.K., Electron Tube Division

314-5, Shimokanzo, Iwata City, Shizuoka Pref., 438-0193, Japan, Telephone: (81)539/62-5248, Fax: (81)539/62-2205

U.S.A.: Hamamatsu Corporation: 360 Foothill Road, P. O. Box 6910, Bridgewater, N.J. 08807-0910, U.S.A., Telephone: (1)908-231-0960, Fax: (1)908-231-1218 E-mail: usa@hamamatsu.com

Germany: Hamamatsu Photonics Deutschland GmbH: Arzbergerstr. 10, D-82211 Herrsching am Ammersee, Germany, Telephone: (49)8152-375-0, Fax: (49)8152-2658 E-mail: info@hamamatsu.de

France: Hamamatsu Photonics France S.A.R.L.: 19, Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: (33)1 69 53 71 00, Fax: (33)1 69 53 71 10 E-mail: infos@hamamatsu.fr

United Kingdom: Hamamatsu Photonics UK Limited: 2 Howard Court, 10 Tewin Road Welwyn Garden City Hertfordshire AL7 1BW, United Kingdom, Telephone: 44-(0)1707-294888, Fax: 44(0)1707-325777 E-mail: info@hamamatsu.co.uk

North Europe: Hamamatsu Photonics Norden AB: Smidesvägen 12, SE-171-41 SOLNA, Sweden, Telephone: (46)8-509-031-00, Fax: (46)8-509-031-01 E-mail: info@hamamatsu.se

Italy: Hamamatsu Photonics Italia: S.R.L.: Strada della Moia, 1/E, 20020 Arese, (Milano), Italy, Telephone: (39)02-935 81 733, Fax: (39)02-935 81 741 E-mail: info@hamamatsu.it

TPMH1089E05
JUL. 2006 IP